

Metallographic Specimen Grinding and Polishing Machine

Kashima-1B/2B



Application & Features

Kashima-1B metallographic specimen grinding and polishing machine is equipped with single disc and features stepless speed changing grinding and polishing. The rotating speed of grinding and polishing disc is adjustable from 50 to 1000rpm. It can realize the whole process of rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing. This machine features easy operation and economical applying. It is the ideal specimen preparing instrument for using in factories, scientific research institutes and laboratories of colleges.

Main Specifications

Model	KASHIMA-1B	KASHIMA-2B
Grinding Disc Diameter	Ø 200mm	
Polishing Disc Diameter	Ø 200mm	
Grinding Disc Rotating Speed	50 - 1000rpm (Stepless Speed)	
Motor	250W	550W
Dimension	400 x 730 x 310mm	700 x 600 x 278mm
Weight	13kg	50kg
Operating Voltage	AC 220V, 50Hz	

Optional Model

Available with double disc model.

