

Metallographic Specimen Grinding and Polishing Machine

# Kashima-1C



## Application & Features

Kashima-1C is equipped with a single disc and features stepless speed of changing grinding and polishing. The rotating speed of grinding and polishing disc is adjustable from 50 to 1000rpm. It can realize the whole process of rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing. This machine features easy operation and economical applying. It is the ideal specimen preparing instrument for using in factories, scientific research institutes and laboratories of colleges.

## Main Specifications

Model	KASHIMA-1C
Grinding/Polishing Disc Diameter	300mm
Grinding Disc Rotating Speed	50 - 1000rpm (Stepless Speed)
Motor	250W
Weight	13kg
Operating Voltage	AC 220V, 50Hz

